


Flanged ceramic package; 2 mounting holes; 2 leads

SOT634A



DIMENSIONS (millimetre dimensions are derived from the original inch dimensions)

UNIT	A	b	c	D	D <sub>1</sub>	E	E <sub>1</sub>	F	L	p	Q	q	U <sub>1</sub>	U <sub>2</sub>	w <sub>1</sub>	w <sub>2</sub>
mm	4.83 3.68	12.82 12.57	0.15 0.08	22.58 22.12	22.56 22.15	13.34 13.08	13.34 13.08	1.14 0.89	5.33 4.32	3.38 3.12	1.70 1.45	27.94	34.16 33.91	13.84 13.59	0.25	0.51
inches	0.190 0.145	0.505 0.495	0.006 0.003	0.889 0.871	0.888 0.872	0.525 0.515	0.525 0.515	0.045 0.035	0.210 0.170	0.133 0.123	0.067 0.057	1.100	1.345 1.335	0.545 0.535	0.010	0.020

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	JEITA			
SOT634A						-01-11-27 03-05-01